


HB200B Chair/light/aspirator	1550	
Tanda R12 Autoclave	680	
HBD Light curing unit	110	
Water distiller	65	
High speed handpiece	85	
Straight handpiece	130	
Contra-angle handpiece	80	
Scaler	110	
Compressor	275	
	US\$3085	£1,570



HB85  
 The rated Working Voltage: AC220V 50HZ  
 Output Power: 850W  
 The start pressure in running: 0.5Mpa(0.1-0.8Mpa)  
 The stop pressure in running: 0.8Mpa  
 The rated exhaust capacity: ≥80L/min(0.4Mpa)  
 The tank cubage: 38L Noise: ≤66db



叠层式灭菌室  
 Piles of chamber

Adopting European N standard with thermal vacuumizing and drying function, it can be used for A type hollow instruments and solid instruments. Thermodynamic vacuum guarantees elimination of cold air from the cavity and make sure of perfect saturation of water dream. Various sterilizing water quantity selections are respectively for different material which embodies the individualized service. Automatic malfunction detecting system makes easy maintaining.

Voltage /Power	Chamber Size	Outside Size	Net weight	Water supply
220V/1400W	192x320	567x441x389	48kg	manual



Sterilization must adopt distilled water as operation medium. even purified water has various minerals and can produce furring scale after evaporation at high temperature, which after a period of time, can lead to leaking of steam due to improper closure. It can also lead to the narrow pipes sensor, to the malfunction of temperature sensor and other failures. Once the furring scale enters handpiece and other instrument which are hollow inside or has apertures, it will clog the narrow pipes and axis, lowering the turning speed of handpiece, thus reducing its life span. therefore, using distilled water is necessary. But since all the dental clinics are located far from each other, it is difficult for them to buy distilled water. Now with DRINK provided you have a reliable source of high quality distilled water as long as you input pipe water! Isn't simple!

Voltage: 220v/50Hz  
 Distilled water: 1.5L/h  
 Chamber size: 18x20  
 Power: 750w  
 Outside size: 290x290x390mm  
 Weight: 3.5kg



Cold shadowless operating lamp  
 X-ray film viewer  
 3-way syringe  
 Dental stool  
 Controllable boweling and cupfilling system  
 Water suction  
 Air suction  
 Adjustable constant temperature cupfilling system

Optional accessories:  
 Imported low speed air motor handpiece  
 Imported air turbine high speed handpiece  
 Ultrasonic scaler  
 Curing light unit

Intra oral camera

Features:

1. Comfortable dental patient chair with somatological design
2. Compact instrument tray which make operation and cleaning easily
3. Rotatable handpiece holder system with more convenience to avoid possible hurtness from handpiece bur against dentist



### **HB-D Light Curing unit**

#### **Feature:**

1. Original imported big power LED from USA
2. High articulation optical fiber
3. Three working modes: strong, gradually strong, flashing
4. Optional working time: 10 sec,15sec,20 sec
5. Automatic inactive, automatic power off
6. Low battery alert
7. Super capacity battery
8. Wireless and corded style

#### **Application:**

Solidify all brands of resin materials

#### **Technical:**

1. Recharger working voltage: AC 100-240V, 50-60HZ
2. Wavelength: 450-480nm
3. Light power: more than 1000mw/cm<sup>2</sup>
4. solidification time and depth: 10s2-3mm